

HALF FACE MASKS - DOUBLE FILTER

Article No.: 2881AV32

Model No.: AV-TP2000R

Main Features:

AVES® AV-TP2000R with two filters is equipped with a synthetic rubber orinasal in single size, an ergonomic harness with four couplings, provided with an head rest adaptable by the user connected to a supporting rigid part. The half mask comprises a frontal exhalation valve and two lateral inhalation valves fitted with special threaded connection mounting two AV-300 series filters, equipped with the same connection.



MATERIALS

AVES® AV-TP2000R half mask is made with the following materials:

- Mask body: synthetic rubber
- Rigid part: polypropylene
- Exhalation valve holder: plastic
- Filter holders: ABS
- Harness + head rest: elastic band + Polypropylene
- Weight (without filters): 140 g

| EN 140:1998 Performance Tests | | EN 140 | AV-TP 2000R |
|-------------------------------|------------------|--------|-------------|
| Total Inward Leakage (%) | | < 2,0 | 0,9 |
| Breathing resistance (mbar) | inhal. 30 l/min | < 0,5 | 0,1 |
| | inhal. 95 l/min | < 1,3 | 0,4 |
| | inhal. 160 l/min | < 2,0 | 1,0 |
| | exhal. 160 l/min | < 3,0 | 2,7 |
| CO2 content (%) | | < 1,0 | 0,4 |

300 SERIES FILTERS

AVES® AV-TP2000R half mask is equipped with gas, particle and combined filters AV-300 series, with special threaded connection, directly screwed to the lateral filter holders. The field of application is different depending on the type of filter used: with particle filters the fields are for example pharmaceutical industry, chemical, building, foundry, agriculture, wood making and with gas and combined filters the fields are shipyard, aeronautics, painting, laboratory.

CERTIFICATION

AVES® AV-2000R half mask meets the requirements of **EN 140:1998 European Standard** and it has the **CE Marking** according to the **European Directive 89/686/EEC, as a PPE of III Category**. Italcert Srl (Notified Body n°0426) is the responsible of the certification (Art. 10) and of the final product control (Art. 11.B). The products are manufactured in a company that is **ISO 9001:2008** certified.

** For the use limitation and all the other informations about the half mask, please refer to the User Information booklet enclosed to each half mask.



QUALITY
INNOVATION
FUNCTIONALITY

| | | |
|---------------|-----------|---------------------|
| Doc. Control: | Rev.: 3.2 | Date: April 6, 2016 |
|---------------|-----------|---------------------|

This Article Data Sheet (ADS) is designed and produced by FLOWTRONIX (FT) covered under the intellectual property law. Any reproduction in whole or in part is strictly prohibited without written approval. FT RP 4013-3.2



AVES[®]



HALF FACE MASKS - DOUBLE FILTER

Article No.: 2881AV32

Model No.: AV-TP2000R

TECHNICAL SPECIFICATIONS

The Thermoplastic rubber orinasal, certified FDA, avoids possible product contaminations. In order to ensure greater fit guarantee, the half mask uses the seal valves developed for the full face masks.



Flaps on the filter connector route the air flow to the entire filtering surface, increasing the efficiency and using the entire surface, increasing its economical value.



Support harness is attached to the rigid body of the half mask, not to the orinasal, therefore it does not mark the user's face and ensures a more uniform fit and comfort.



The flexible strap allow a simple and safe adjustment of the harness.



Vortex technology



Balanced
Better distribution of weight on mask, better stability



Airy
3 flaps on filter holders generate a lamellar air flow, reduce breathing resistance & increase filter life span



Intuitive
Filter is easy to lock in thanks to thread connection



Resistant
Thread connection withstands time wear



QUALITY
INNOVATION
FUNCTIONALITY

| | | |
|---------------|-----------|---------------------|
| Doc. Control: | Rev.: 3.2 | Date: April 6, 2016 |
|---------------|-----------|---------------------|

This Article Data Sheet (ADS) is designed and produced by FLOWTRONIX (FT) covered under the intellectual property law. Any reproduction in whole or in part is strictly prohibited without written approval. FT RP 4013-3.2





HALF FACE MASKS - DOUBLE FILTER


Article No.: 2881AV32

Model No.: AV-TP2000R

TECHNICAL SPECIFICATIONS

WEARING HALF FACE MASK

1. Screw the filters tightly onto the breathing apparatus, making sure that the rubber washer is in place at the base of the thread on the mask itself.



2. Slacken both harnesses to their maximum extent, then put your head into the harness, and place the half face mask over nose and mouth. With the other hand, position and tighten the harness on your head.



3. Adjust each harness strap individually to achieve a good fit of the mask to your face.



LEAK TEST

4. Press your palm against the filters for closing down the exit of the air. If trying to inspire you don't perceive air leaks between the face and the half mask, it means that the mask is well positioned and sealed.

Otherwise, we need a better placement on the face and possibly to increase the tension of the harness. Repeat the operation until you get a good seal.



CLEANING

5. The half face mask must be cleaned after each use. First remove the two filters, and blow dust from the mask. Use warm water containing a neutral detergent. Never use solvents. Disinfect with a normal disinfectant that will not damage plastic or rubber components. Dry rubber parts at a temperature below 50°C.

STORAGE

6. When storing the mask, hold in a closed packaging and make sure that it is protected by dust and dirt, light, humidity and heat.

** For the use limitation and all the other informations about the half mask, please refer to the User Information booklet enclosed to each half mask.



QUALITY
INNOVATION
FUNCTIONALITY

This Article Data Sheet (ADS) is designed and produced by FLOWTRONIX (FT) covered under the intellectual property law. Any reproduction in whole or in part is strictly prohibited without written approval. FT RP 4013-3.2

| | | |
|---------------|-----------|---------------------|
| Doc. Control: | Rev.: 3.2 | Date: April 6, 2016 |
|---------------|-----------|---------------------|



Certificate of Conformity

The authorised manufacturer

FLOWTRONIX FZE

P.O. Box: 17154, Jebel Ali - Jafza, Dubai, United Arab Emirates

declares that the personal protective equipment described hereafter:

Product Reference

AV-TP2000R
Article No.: 2740AV32
AVES®-BLS®

Classification

CE EN 140:1998

Description:

Haft face mask with double filter connectors

- Thermoplastic Rubber Face Seal
- Rigid part: Polypropylene
- Plastic exhalation valve holder
- Harness + Head rest: Elastic band + Polypropylene



- are in conformity with the provisions of Council Directive 89/686/EEC and subsequent modifications (Directives 93/95/EEC, 93/68/EEC and 96/58/EC) and with the national standard transposing harmonized standard

CE EN 140:1998

- is identical to the PPE that is the subject of the EC Type-Examination Certificate No. PPE/AT n° 018-95 Rev.1 - Est. 02-05/00 0195/07

EC compliance certificate delivered by the notified body
Italcert S.r.l. – Viale Sarca, 336 - 20126 Milano Italy
(Notified Body No. 0426)